SIEMENS

SIWAREX R Load Cells

Operating Instructions

Edition 06/2009



Table of Contents:

	Safety Instructions	3
	General Information	4
	Notes on product liability	4
1	Technical Description	5
1.1	Area of Application	5
1.2	Structure	5
1.3	System Configuration	7
2	Installation/Assembly	10
2.1	Installation	10
2.2	Assembly	13
2.3	Disassembly	16
3	Commissioning	17
4	Service	19
4.1	Care and Maintenance	19
4.2	Troubleshooting	19
5	Technical Data	22
5.1	Functional Data	22
5.2	Unit Version	24
5.3	Explosion Protection	25
5.4	Electromagnetic Compatibility	26
5.5	Dimensions	27
6	Ordering Data	

Safety Instructions



DANGER

indicates that death, severe personal injury or substantial property damage **will** result if proper precautions are not taken.



WARNING

indicates that death or severe personal injury **can** result if proper precautions are not taken.



CAUTION

This text accompanied by a warning triangle indicates that minor personal injury can result if proper precautions are not taken.

CAUTION

This text without an accompanying warning triangle means that property damage may occur if proper precautions are not taken.

ATTENTION

indicates that an undesirable result or state may result if the proper steps are not taken.

NOTE

indicates a potential benefit if recommendations are followed.

Qualified personnel as used in the safety instructions in this manual and on the product itself are individuals who are familiar with the installation, assembly, initial start-up and operation of this product. They must be authorized and qualified to install, start and maintain devices, systems and circuits in accordance with national safety rules and regulations.

Copyright © Siemens AG 2009 All rights reserved

The reproduction, transmission or use of this document or its contents is not permitted without express written authority. Offenders will be liable for damages. All rights, including rights created by patent grant or registration of a utility model or design, are reserved.

Disclaimer of Liability

We have checked the contents of this manual for agreement with the hardware and software described. Since deviations cannot be precluded entirely, we cannot guarantee full agreement. However, the data in this manual are reviewed regularly and any necessary corrections included in subsequent editions. Suggestions for improvement are welcomed.

Siemens AG Bereich Automatisierungs- und Antriebstechnik Geschäftsgebiet Process Instrumentation and Analytics D-76181 Karlsruhe

©Siemens AG 2009 Technical data subject to change.

General Information

Use for the intended purpose

Use for the intended purpose means that this product may only be used within the limits of the technical specifications and statement of purpose of this operating manual.

This device will not be a source of danger provided it is used for the intended purpose under consideration of the safety instructions.

Perfect, safe operation of this device is conditional upon proper transport, storage, installation and assembly.

Proper operation of this device can only be ensured if the specifications provided in technical data are observed.

Improper handling can result in death, severe personal injury and property damage.

Notes on product liability

We expressly point out that the nature of the product is described exclusively and conclusively in the contract of sale. The contents of this product documentation are not part of an earlier or existing agreement, acceptance or legal relationship nor do they affect these in any way. The particular contract of sale determines the sum of obligations to be met by Siemens and the guarantee regulation container therein is complete and is the sole regulation that shall apply. This contractual guarantee regulation is neither extended nor limited by the information provided in this document.

Information on delivery

The scope of delivery in accordance with the valid contract of sale is listed in the shipping documents enclosed in the delivery.

Please observe any relevant instructions when opening the packaging. Check the shipment for completeness and possible transportation damage. In particular, compare the order number on the rating plate with the order information.

Please read this operating manual before starting work! It contains important information and data that, if observed, ensure the overall safety and functionality of this device. Following these instructions will make it easier for you to use handle this product and ensure reliable measuring results.

1 Technical Description

1.1 Area of Application

SIWAREX R load cells are used for static and dynamic measurements of forces and weights. They can be used for almost all applications in industrial weighing technology. These may be for example:

- · container, hopper or platform scales,
- · rollway, belt or crane scales,
- filling/packing plants, proportioning and mixing,
- filling level and completeness inspection,
- equipment for monitoring pressing and clamping procedures,
- dynamic scales

(figure 1-1)

All applications can be located in areas with mandatory calibration or in hazardous areas.

1.2 Structure

The SIWAREX R load cells are equipped with wire strain gauges (WSG). WSG load cells are transducers for converting mechanical forces into electrical signals. The functional principle is always the same despite different designs. The basic element is a special spring body. The spring body is deformed elastically when a force is applied. The integrated WSGs then change their ohmic resistance




Figure 1-1 Principle diagram shown by the example of a bending rod load cell

At least four WSGs per load cell are connected in a full Wheatstone bridge. The stretched or upset WSGs are wired so that the positive or negative changes in resistance add up to a total upset of the bridge.

The feed voltage (in 6-wire technology also the sensor voltage, SENSE) is applied at one bridge diagonal. The measuring voltage is tapped at the other diagonal. At a constant feed voltage (EXC), the measured voltage (SIG) changes proportionally to the applied load (figure 1-2). In practice load cells contain other resistors for temperature compensation, zero point and parameter adjustment. These may be in the input or output of the load cell depending on the type and on requirements.




Figure 1-2 Principle diagram of a Wheatstone bridge

The SIWAREX R load cells are usually made of high-grade steel and are welded hermetically sealed. This provides high corrosion protection and protection rating. Most series are licensed for use in scales with mandatory calibration of class III according to DIN EN 45501 and comply with OIML R60 3000d. Load cells with greater accuracy and/or EEx (i) approval are available on request. SIWAREX R load cells are electrically calibrated as standard. As a result, no reference load adjustment is necessary for example when commissioning a platform scales. A load cell can also be exchanged without readjustment. An exception to this rule is the series K and possibly load cells delivered outside the standard scope of delivery. The respective technical data apply for these load cell types.

1.3 System Configuration

In weighing technical systems one or more load cells are connected to a weighing module for evaluation of the measured signal. Several load cells of a scales are connected in parallel in a junction box to supply a common output signal.

Load cells may only be connected in parallel when they have the same characteristic value, the same rated load and the same internal resistance.

ATTENTION

The total resistance in parallel connected load cells may not drop below the minimum resistance specified in the technical data of the weighing module.

The maximum number of load cells that can be connected to a weighing module depends on the total resistance of the parallel connected load cells. This must be within limits of the weighing module specified for the load resistance. The length of the lines and the data of other elements, e.g. Ex i-Interface, must also be taken into account.

CAUTION

If several load cells are connected in a scales it cannot be determined whether individual load cells are overloaded in the event of uneven load distribution.

The maximum cable length between the load cell and the weighing module can be found in the technical data of the weighing module. For Ex applications the data of the Ex-i interface must also be taken into account.

A shielded 6-wire cable, e.g.. Li2Y(ST)CY 6x0.75 mm², Siemens order no.: 7MH4 702-8AB or, for Ex applications, 7MH4 702-8AA must be used to connect the junction box to the weighing module, to extend a load cell connecting cable or for a cross-connection between two junction boxes.

Overloads should be avoided in the layout of load cells by creating a safety reserve. The safety reserve for three application points should be 20%. In the case of statically aspecific use of more than three application points, the safety reserve must be at least 50% if it cannot be ruled out that the load is only resting on two diagonally opposite load cells. The reason for this may be drops in the foundation or improper assembly. Accidental overloads or overloads due to the process must be taken into account or kept away from the load cells by overload protection devices. Overloads are caused for example:

- in the case of uneven load distribution as a result of attachments or tipping mounds.
- when rolling/pushing the load onto platform or rollway scales,
- by hard setting down of the load,
- by setting down the load in free fall,
- when persons are leaning/standing on the scales,
- by wind forces on the side of a silo facing away from the wind.

Overloads may also occur in lifting direction when the force application is permanently mounted to the load cell such as elastomer bearings on load cells of series BB.

Lift off protection is necessary where there is a risk of the load carrier lifting off or tipping over. This is essential for lightweight containers or high silos outdoors.

CAUTION

Overload protection devices must always be provided for load cells with low rated loads to protect the cells from being damaged.

Use of the load cells beyond the maximum working load or maximum transverse load can lead to irreparable faults and even breakage of the load cell. Load cells may not be overloaded, e.g. by tightening screws, when adding installation components.

NOTE

If load cells are loaded beyond their rated load this can lead to an error message in the weighing module.

If load surges during the measuring mode cannot be ruled out, for example when the load is set down in free fall, suitable precautions must be taken to avoid damage to the load cell (e.g. elastomer bearings or higher load cells).

The load must be applied in exact measuring direction of the load cell. Torsion and bending torques, off-center loads and transverse loads are disturbances which on the one hand falsify the measuring result and on the other hand can damage the load cell when they exceed the permissible limits. Load cells must therefore be installed with suitable installation components (e.g. SIWAREX R installation components). The possible errors mentioned above are then largely avoided. The installation components allow enough freedom of movement to prevent heat expansion leading to transverse loads.

Transverse forces such as are caused by wind, acceleration or conveyor belt friction must be compensated by deflections or stops. Deflections must be installed exactly vertical to the direction of action of the load cells so that no force components occur in measuring direction. The deflections must be installed in such a way that they do not twist for example when the application points expand. This is most easily avoided by arranging the deflections in the same direction of rotation.

The deflections to be installed should correspond to the principles used in weighing technology. Ball-jointed deflections are available for most SIWAREX R combinistallation units. Ball bolt deflectors up to a transverse load of 1000 kN are available on request.

No parallel forces may be applied by filling and emptying devices and supply lines.



DANGER

Load cells are machine elements not constructed with the usual safety factors. Therefore appropriate crash protection or catastrophe protection must be provided which suit the danger potential.

CAUTION

For protection against undesirable electrical currents such as they occur when welding or from lightning, the load cells must be bridged with a highly flexible grounding cable (e.g. SIWAREX R grounding cable 7MH3 701-1AA1).

The substructure must withstand the planned loads. The application surface must have a roughness of a max. 1.6 μ m.

The values in the technical data must be observed for the ambient conditions.

Note

The load cell must be protected from direct sunlight. The permissible operating temperature could otherwise be exceeded and thus the accuracy impaired.

2 Installation/Assembly

2.1 Installation

SIWAREX R load cells may only be assembled and connected by qualified personnel.

If a scales is equipped with a single load cell, this can be connected directly to the weighing module if space allows. To bridge greater distances the connecting cable can be extended through a junction box.

Several load cells are connected in parallel in a junction box.

Load cells can be fitted with 4 or 6-wire connecting cables.

Four-wire connecting cables should not be shortened or lengthened because the line resistance is temperature-compensated. If the length of the connecting cable is altered, the input and output resistance also changes. This change can be corrected by adjusting the scales but this does not compensate temperature-related changes in resistance of the missing or lengthened piece of cable. The value of the remaining temperature error is shown in the table below. The SIWAREX measuring cable 7MH4702-8AA / -8AB is used as the basis for these observations. The feed lines are connected in parallel (double).

Table 2-1 Remaining temperature error of a cell per 10 K in %:

Change in			Series		
length	K	RN	BB	CC	SB
3 m	0.0012	0.0003	0.0007	0.0007	0.0009
5 m	0.0020	0.0005	0.0012	0.0011	0.0014
10 m	0.0040	0.0009	0.0024	0.0022	0.0029

If 3 or 4 cells are operated in parallel and the cable of a cell is lengthened, the additional error is about a third or a quarter. Prerequisite is an even load distribution on the cells.

ATTENTION

Only EMC-safe housings (e.g. SIWAREX JB) may be used to extend connecting cables.

On 6-wire connecting cables, the feed voltage is fed back as a reference voltage to the weighing module. Shortening or lengthening has no effect on the measuring result.

Figures 2-1 and 2-2 show the parallel connections of load cells in 4 and 6-wire technology.

ATTENTION

If load cells with 4-wire connecting cables are used, two bridges must be inserted additionally:

Bridge 1: EXC- to SENSE-Bridge 2: EXC+ to SENSE+




Figure 2-1 Parallel connection in 4-wire technology




Figure 2-2 Parallel connection in 6-wire technology

Table 2-2 shows the color codes and signal assignment of the connecting cables.

Table 2-2 Color codes and signal assignment

oad cell series		le connection
_	Function	Color
3B	EXC+	green
	EXC-	black
	SIG+	white
	SIG-	red
	Shield	transparent
SB	EXC+	green
	EXC-	black
	SIG+	white
	SIG-	red
	Shield	transparent
RN	EXC+	pink
	EXC-	gray
	SIG+	brown
	SIG-	white
	Shield ¹⁾	transparent
CC	EXC+	green
	EXC-	black
	SIG+	white
	SIG-	red
	Shield	transparent
SP	EXC+	green
	EXC-	black
	SIG+	white
	SIG-	red
	Sens+	vellow
	Sens-	blue
	Shield	transparent
K	EXC+	red
	EXC-	white
	SIG+	black
	SIG-	blue
	Shield	transparent

⁻ Shield placed on load cell housing

See the data sheet for color codes of load cells not listed.

2.2 Assembly

Load cells are high-precision components and must be handled with care especially during transportation and assembly.

CAUTION

Mechanical shock or dropping can cause irreparable damage to the load cell. Load cells may not be carried by the connecting cables.

⁻ Shield not fed out of connecting cable

As long as the assembly work on the scales has not been completed, the load cells should be replaced by dummies to protect them against impact or welding currents.

CAUTION

If welding should be necessary after load cells have been installed, make absolutely sure that the welding current is not conducted through the load cell. The ground clamp of the welding gear should be attached directly next to the welding point with a safe contact. The load cells must be bridged with the grounding cable. The individual load cells must be disconnected.

Load cells may not be overloaded. The load carrier should be set down slowly. IN load cells with low rated loads in particular there is a danger that the load cell body could be distorted by application of force, e.g. tightening lock nuts.



WARNING

Suitable lifting gear must be used for lifting the load carrier. The appropriate safety regulations must be observed.

The bearing is statically indefinite in the case of more than three load cells or application points. The force application points should be at the same height. The output signals of all load cells should be approximately the same at even load or correspond to the load distribution in the case of uneven load. Proceed as follows to measure the load on the load cells:

- Disconnect load cell cables SIG+ and SIG-.
- Supply load cells with the feed voltage (e.g. 10.2V).
- Measure the output voltages between SIG+ and SIG- of the individual load cells.

The measured voltage corresponds in proportion to the product of characteristic value times supply voltage to the weight percentage at the rated load which is applied to the load cell.

Example: feed voltage U_s 10.2V

 $\begin{array}{lll} \text{characteristic value} & C_n \ 2\text{mV/V} \\ \text{rated load} & E_{\text{max}} \ 5\text{t} \\ \text{output voltage} & U_a \ 4\text{mV} \end{array}$

Calculation: $4mV / (10,2V \times 2mV/V) = 0.196$

 $0.196 \times 5t = 0.98t$

Result: The load cell is loaded with 0.98t

Spacer plates should be placed beneath the load cell with the lowest value until the output voltages are adjusted equally.

The load cell seat must be horizontal, completely level and, like the load cell base, absolutely clean.

The contact surfaces of the force applications must be lubricated with highperformance grease. If overload protection devices are available, these must be set so that they still accommodate the desired load safely. They must allow an unhindered increase in weight up to the nominal weight.

Overload protection devices must be protected against soiling and freezing. The perfect functioning of overload protection devices must be checked in the course of regular maintenance work.



DANGER

Soiled, frozen or incorrectly set overload protection devices block and lead to faulty measurements or can cause overflowing of the scales with property damage and injury to persons.

CAUTION

Correct assembly of the load cell and installation element must be checked by inspecting the installation dimensions and pendulum travel for example. Make sure the cable is not damaged or cut.

The cable must be laid at the cable glands in the form of a vertical downward loop to avoid penetration by water.

CAUTION

The installation regulations of the installation element must also be taken into account in assembly.

Special features of bending ring scales series RN, RH, RC, RS

- Bending ring scales up to 13t are delivered with a pressure piece. The
 pressure piece is inserted in the load cell and secured against falling out by
 adhesive tape. It may not be lost when handling the load cell.
- Bending ring load cells have a very small measuring distance. An overload protection is integrated in load cells with rated loads up to 13t. The standing area of the load cell restricts the movement of the force application tube. For this reason the standing area of the load cell must be checked carefully for soiling prior to installation. If there is a risk that the bottom of the load cell could become soiled or frozen, appropriate inspection and/or sealing measures must be taken. The bottom can be protected by a grease ring or sealing compound for example. When these measures are taken it must be considered that the force application also needs to be well sealed at the top of the load cell to effectively prevent penetration by moisture.

2.3 Disassembly

The same safety regulations and conditions apply for disassembly of the load cells as for installation and assembly.

- Switch off all energy and power supplies.
- Secure the load carrier against falling.
- Use suitable lifting gear and tools.
- Relieve load on the load cell and remove carefully without using force.
- Do not cut the cable if the load cell is to be used again or sent in for repair.
- Do not carry or pull the load cell by the cable.

3 Commissioning

The load cells are passive sensors. The manual of the weighing module should therefore be consulted primarily for commissioning. When using in the Ex area, the instructions for the Ex-i interface or Ex barrier must be observed.

If the reference load of a scales needs to be checked, impermissibly great deviations in the weight display may occur in load cells which are not electrically calibrated. This reference load error can be electrically compensated. To do this, the individual measured values are adjusted to the smallest measured value by additional wiring. The resistors are connected in series with the load cell measuring signal. The measuring voltage is reduced by the appropriate resistance until it is equal to the smallest voltage. Because the resistors are connected in the measuring circuit, the temperature coefficient must be accordingly low (0.25ppm/K to 10ppm/K)

Example for reference load adjustment:

Platform scales with 4 load cells, series RN, rated load L_n =500kg, rated characteristic value C_n =2.0mV/V, test weight =150kg.




Figure 3-1 Test diagram

Procedure:

Measure output resistances R_a of the LC or take them from the data sheet

LC 1 = 1004.52Ω

LC 2 = 1003.64Ω

LC 3 = 1010.70Ω

LC $4 = 1028.12 \Omega$

Edition 06/2009 Commissioning

• Apply test weight to all 4 corners and note values:

LC 1 = 160kg LC 2 = 148kg LC 3 = 155kg LC 4 = 152kg

Determine differences to the smallest value (148kg):

```
LC 1 - LC 2 = 160kg - 148kg = 12kg
LC 3 - LC 2 = 155kg - 148kg = 7kg
LC 4 - LC 2 = 152kg - 148kg = 4kg
```

Calculate correction resistance:

```
R_{corr} = R_a x L_{error} / L_{test}

LC 1: R_{corr} = R1 = 1004.52 Ω x 12kg / 150kg = approx. 80 Ω

LC 2: smallest value -> no resistance necessary

LC 3: R_{corr} = R3 = 1010.70 Ω x 7kg / 150kg = approx.47 Ω

LC 4: R_{corr} = R4 = 1028.12 Ω x 4kg / 150kg = approx. 27 Ω
```

 R_{corr} = determined correction resistance (to be installed in the measuring line SIG+)

R_a = output resistance of the load cells (can also be measured in the loaded state)

 L_{error} = weight error (difference value from the smallest weight value) L_{test} = test load (applied at all corners)

Install resistors and repeat test




Figure 3-2 Circuit diagram reference load adjustment

4 Service

4.1 Care and Maintenance

Load cells are principally maintenance-free. However, regular inspections with checking of the force applications, pendulum limits, lift off and overload protections increase the reliability. The inspections should also be carried out after serious events such as thunderstorms, floods or earthquakes.

If signs of corrosion appear, these can be counteracted by suitable protective coatings.

Accumulation of dirt in the vicinity of a load cell should not be tolerated. When cleaning with a high-pressure water jet, the jet may not be directed at the cable gland or other sealing elements.

4.2 Troubleshooting

If errors or wrong measuring results occur which can be traced to the load cells, the following points should be checked:

- Are there parallel forces, e.g. due to cables, pipes or guides which exert force in measuring direction?
- Are there any other disturbances caused by soiling or thermal expansion?
- Are all the load cells aligned correctly horizontally and at the same height?
- Has moisture penetrated the junction box?
- Are the cables connected correctly?
- Are cables damaged?

A defective load cell of a weighing system can be localized by corner loading or disconnection of the individual load cells. To check load cells for a defect, the following measurements are necessary:

Zero signal:

- Remove load completely from the load cell to be tested.
- · Disconnect all load cells.
- Supply the load cell to be tested with approx. 10V DC (weighing module or external power supply).
- Measure voltage between SIG+ and SIG-.
- Divide measured voltage by the feed voltage.

The result must match the value in the data sheet.

Edition 06/2009 Service

Insulation resistance

- Disconnect the load cell.
- Connect all lines.
- Measure insulation resistance between lines and load cell housing
- Measure insulation resistance between lines and cable shield
- Measure insulation resistance between cable shield and load cell housing (This
 measurement is not possible in load cells in which the shield is connected to
 the load cell housing).

The insulation resistance must match the value in the technical data

Input and output resistance

- Disconnect the load cell.
- Measure the input resistance between EXC+ and EXC-.
- Measure the output resistance between SIG+ and SIG-.

The resistances must match the values in the data sheet or the technical data.

Bridge resistance

- Disconnect load cell.
- Measure resistance between SIG- and EXC-
- Measure resistance between SIG+ and EXC+

The difference between the two values may not be greater than 1Ω .

The measurement cannot be made in the series K load cell.



DANGER

Measurements may not be made on the load cells in the Ex area.

CAUTION

Do not use ohmmeters which feed more voltage into the load cell than permitted in the technical data to measure the resistance.

A frequent cause of error which leads to failure of the load cells is their overloading. If overloading is diagnosed as the cause of the error, further measures are necessary. Damage is often caused by one of the following:

1. Dynamic overloading, e.g. by accidental falling of a relatively small weight onto the load carrier from a great height.

Possible remedies:

- Fit shock-absorbing components, e.g. elastomer bearings
- Overdimension the load cells

Edition 06/2009 Service

2. <u>Transverse forces</u>, e.g. by pushing on or braking loads on a platform.

Possible remedies:

- Install deflectors
- Install pendulum limits or set closer together.

NOTE

Only send in defective load cells to our repair workshop with an exact description of the error. This makes troubleshooting and analysis easier.

5 **Technical Data**

5.1 **Functional Data**

	BB series	CC series		K series
	- C	SERMINS BANKE IN REQUEST CARE OF COST TO COST VIN DOCUMENTS VIN DOCUMENTS		Services ("mark booses" (" 10 avy
Possible applications	Container, Conveyor, platform scales	Container, hopper, vehicle scales		Container, hopper scales
Туре	Bending beam	Pressure force		Pressure force
Rated load/maximum load E_{max}	10/20/50/100/200/350 kg	10/25/40/60 t	100 t	2.8/6/13/28/60/130/280 t
Accuracy class according to OIMLR60	C3	C3	C1	0.2%
Max. scale interval n_{LC}	3000	3000	1000	
Min. scale interval V_{\min}	E _{max} /15000	E _{max} /12500	E _{max} /10000	
Minimum application range R _{min(LC)}	20 %	24 %	10 %	
Combined error F _{comb}	$\leq \pm 0.02 \% C_{n}$	$\leq \pm 0.02 \% C_{n}$	$\leq \pm 0.03 \% C_{n}$	< 0.2 % C _n
Deviation F _v	$\leq \pm 0.01 \% C_{n}$	$\leq \pm 0.01 \% C_{\rm n}$	$\leq \pm 0.02 \% C_{\rm n}$	-
Return of zero signal	$\leq \pm 0.0167 \% C_n^{-1}$	$\leq \pm 0.0167 \% C_n^{-1}$	$\leq \pm 0.05 \% C_n^{1)}$	-
Creepage error F _{cr}				
• 30 min	$\leq \pm 0.0245 \% C_n^{-1}$	$\leq \pm 0.0245 \% C_n^{-1}$	$\leq \pm 0.049 \% C_0^{-1}$	-
• 20 to 30 min	$\leq \pm 0.0053 \% C_n^{-1}$	$\leq \pm 0.0053 \% C_n^{-1}$	$\leq \pm 0.0105 \% C_n^{-1}$	-
Temperature coefficient				
 Zero signal T_{Ko} 	$\leq \pm 0.0045 \% C_0/5K$	$\leq \pm 0.0056 \% C_n/5K$	≤ ± 0.007 % C _n /5K	$\leq \pm 0.25 \% C_{\rm p}/5K$
Characteristic value T _{Kc}	≤ ± 0.0045 % C _n /5K	$\leq \pm 0.0045 \% C_0/5K$	≤ ± 0.0085 % C _n /5K	$\leq \pm 0.25 \% C_{\rm n}/5K$
Min. initial loading E_{min}	0 % E _{max}		% E _{max}	0 % E _{max}
Max. work load L	150 % E _{max}		% E _{max}	120 % E _{max}
Break load L _d	300 % E _{max}		% E _{max}	300 % E _{max}
Max. lateral load L_{lq}	100 % E _{max}		% E _{max}	10 % E _{max}
Rated measuring path h_n at E_{max}	0.3 ± 0.03 mm		0.36 mm	0.23 to 2.67 mm
Overload protection	-	THURST.	-	-
Supply voltage U_{sr} (reference value)	10 V	1	0 V	6 V
Supply voltage (range)	5 to 15 V		25 V	6 to 12 V
Rated characteristic value C_n	2 mV/V		mV/V	1.5 mV/V
Tolerance D_c of characteristic value	± 1 %		1 %	± 0.5 %
Tolerance D_0 of zero signal	≤ ± 1 % C _n		1 % C _n	≤ ± 1.5 % C _n
Input resistance R_e	460 Ω ± 50 Ω		0 ± 4.5 Ω	etwa 275 Ω
Output resistance R _a	350 Ω ± 3.5 Ω		2 ± 4.8 Ω	245 Ω ± 0.2 Ω
Insulation resistance R _{is}	≥ 5000 MΩ		000 ΜΩ	≥ 20 MΩ
Rated temperature range B_{tn}	-10 to +40 °C) +40 °C	-10 to +60 °C
Operating temperature range B_{tt}	-40 to +80 °C) +80 °C	-20 to +70 °C
Storage temperature range B_{ts}	-40 to +90 °C		+90 °C	-30 to +80 °C
Sensor material (DIN)	Stainless steel 1.4542		steel 1.4542	Steel. painted
Degree of protection to DIN EN 60529, IEC 60529			6/IP 68	IP 65
Max. tightening torque of the fixing screws	23 Nm		-	-
Current calibration 2)	Standard	Sta	ndard	-
EEx (i) certification 3)	EEx ib II C T6	EEx ib	II C T6 4)	-

¹⁾ For rated temperature -10 to +40 °C
²⁾ Current calibration: nominal characteristic value and output resistance are adjusted so that the output current is calibrated within 0.05 % of a reference value. This makes it easier to connect several load cells in parallel.

³⁾ Optional
4) EEx(d) version on request (only 40/60 t)

RN series



SB series



Possible applicatons	Container, conveyor, platform and roller table scales			Container, conveyor, overhead rail and platform scales
Туре	Bending ring			Shear beam
Rated load/maximum load E _{max}	60/130/280 kg	0.5/1/2/3.5/5/10 t	13/28/60 t	0.5/1/2/5 t
Accuracy class according to OIMLR60	C3	C3	C3	C3
Max. scale interval n _{LC}	3000	3000	3000	3000
Min. scale interval V _{min}	E _{max} /17500	$E_{\text{max}}/10000$	E _{max} /17500	E _{max} /10000
Minimum application range R _{min(LC)}	17 %	30 %	17 %	30 %
Combined error F _{comb}	$\leq \pm 0.018 \% C_n$	$\leq \pm 0.023 \% C_n$	$\leq \pm 0.018 \% C_{n}$	$\leq \pm 0.02 \% C_{n}$
Deviation F _v	$\leq \pm 0.01 \% C_{n}$	$\leq \pm 0.01 \% C_{\rm n}$	$\leq \pm 0.01 \% C_{n}$	$\leq \pm 0.01 \% C_{n}$
Return of zero signal	$\leq \pm 0.0167 \% C_n^{-1}$	$\leq \pm 0.0167 \% C_n^{-1}$	$\leq \pm 0.0167 \% C_n^{-1}$	$\leq \pm 0.0167 \% C_n^{-1}$
Creepage error F _{cr}				
• 30 min	$\leq \pm 0.0120 \% C_0^{-1}$	$\leq \pm 0.0245 \% C_n^{-1}$	$\leq \pm 0.0120 \% C_n^{-1}$	$\leq \pm 0.0245 \% C_n^{-1}$
• 20 to 30 min	$\leq \pm 0.0053 \% C_n^{-1}$	$\leq \pm 0.0053 \% C_0^{-1}$	$\leq \pm 0.0053 \% C_n^{-1}$	$\leq \pm 0.0053 \% C_0^{-1}$
Temperature coefficient				
 Zero signal T_{Ko} 	≤ ± 0.007 % C _v /5K	≤ ± 0.007 % C _n /5K	≤ ± 0.007 % C ₀ /5K	≤ ± 0.007 % C _n /5K
Characteristic value T _{Kc}	$\leq \pm 0.0045 \% C_0/5K$	≤ ± 0.0045 % C ₀ /5K	≤ ± 0.0045 % C _n /5K	$\leq \pm 0.0045 \% C_{n}/5K$
Min. initial loading E_{min}	0 % E _{max}	0 % E _{max}	0 % E _{max}	0 % E _{max}
Max. work load L_{ii}	200 % E _{max}	150 % <i>E</i> _{max}	150 % E _{max}	150 % E _{max}
Break load L _d	500 % E _{max}	300 % E _{max}	300 % E _{max}	300 % E _{max}
Max. lateral load L_{lo}	75 % E _{max}	100 % E _{max}	75 % E _{max}	100 % E _{max}
Rated measuring path h_0 at E_{max}	0.07 mm	0.1 ± 0.02 mm	0.11 - 0.2 mm	≤ 0.5 mm
Overload protection	Integrated	Integrated	Integrated for 13 t	2 0.3 mm
Supply voltage U_{sr} (reference value)	15 V	10 V	15 V	10 V
Supply voltage (range)	5 to 30 V	5 to 30 V	5 to 30 V	5 to 18 V
Rated characteristic value C_n	1 mV/V	2 mV/V	2 mV/V	2 mV/V
Tolerance D_c of characteristic value	± 0.01 mV/V	± 0.1 mV/V	± 0.1 mV/V	± 1 %
Tolerance D_0 of zero signal	± 0.01 1110/ V ≤ ± 1 % C _n	± 0.1 1110/V ≤ ± 1 % C _n	± 0.11110/V ≤ ± 1 % C _n	± 1 % C _n
Input resistance R_e	1260 Ω ± 100 Ω	1110 Ω ± 50 Ω	13 t 1200 Ω ± 100 Ω	350 Ω ± 3.5 Ω
input resistance Re	1200 12 ± 100 12	1110 12 ± 30 12	28 t 1075 Ω ± 100 Ω	330 12 ± 3.5 12
			60 t 1350 Ω ± 100 Ω	
Output resistance R _a	1020 Ω ± 0.5 Ω	1025 Ω ± 25 Ω	13 t 1000 Ω ± 0.5 Ω	350 Ω ± 3.5 Ω
Output resistance R _a	1020 12 ± 0.3 12	1023 17 ± 23 17	28 t 930 Ω ± 0.5 Ω	330 12 ± 3.5 12
			60 t 1175 Ω ± 0.5 Ω	
Insulation resistance R _{is}	≥ 20 MΩ	≥ 5000 MΩ	≥ 20 MΩ	≥ 5000 MΩ
Rated temperature range B_n	-10 to +40 °C	-10 to +40 °C	-10 to +40 °C	-10 to +40 °C
	-30 to +85 °C	-10 to +40 °C	-10 to +40 °C -30 to +85 °C	-10 to +40 °C
Operating temperature range B _{tu}	-50 to +85 °C	-50 to +70 °C	-50 to +85 °C	-40 to +80 °C
Storage temperature range Bts				
Sensor material (DIN)	Stainless steel 1.4542	Stainless steel 1.4542 IP 66/IP 68	Stainless steel 1.4542 IP 66/IP 68	Stainless steel 1.4542 IP 66/IP 68
Degree of protection to DIN EN 60529, IEC 60529			IF 00/IP 00	
Max. tightening torque of the fixing screws	8 Nm	14 Nm (0.5 t to 5 t)	-	110 Nm (0.5 to 2 t) 540 Nm (5 t)
Current calibration 2)	Standard	Standard	Standard	Standard
EEx (i) certification 3)	EEx ib II C T6	EEx ib II C T6	EEx ib II C T6	EEx ib II C T6

 $^{^{1)}}$ For rated temperature –10 to +40 $^{\circ}\text{C}$

See the data sheet for technical data of unlisted load cells.

²⁾ Current calibration: nominal characteristic value and output resistance are adjusted so that the output current is calibrated within 0.05 % of a reference value. This makes it easier to connect several load cells in parallel.

³⁾ Optional

SP series



Possible applications	Small platform scales, small conveyor scales
Туре	Single point
Rated load/maximum load E _{max}	6/12 kg
Accuracy class according to OIMLR60	C3
Max. scale interval n _{LC}	3000
Min. scale interval V _{min}	E _{max} /12000
Minimum application range $R_{min(LC)}$	25 %
Combined error F _{comb}	$\leq \pm 0.02 \% C_{n}$
Deviation F _v	\leq ± 0,01 % C_{n}
Return of zero signal	$\leq \pm 0.0167 \% C_n^{-1}$
Creepage error F _{cr}	
• 30 min	$\leq \pm 0.0245 \% C_n^{(1)}$
• 20 to 30 min	$\leq \pm 0.0053 \% C_n^{-1}$
Temperature coefficient	
 Zero signal T_{Ko} 	$\leq \pm 0,0058 \% C_{n}/5K$
Characteristic value T _{Kc}	≤ ± 0,0045 % C₀/5K
Min. initial loading E _{min}	0 % E _{max}
Max. work load L	150 % E _{max}
Break load L _d	300 % E _{max}
Max. lateral load L _{lg}	100 % E _{max}
Rated measuring path h_n at E_{max} 6 kg	0,24 ± 0,02 mm
Rated measuring path h_0 at E_{max} 12 kg	0,19 ± 0,01 mm
Supply voltage U_{sr} (reference value)	10 V
Supply voltage (range)	5 to 15 V
Rated characteristic value C_n	2 mV/V
Tolerance D _c of characteristic value	± 10 %
Tolerance D₀ of zero signal	≤ ± 1 % C _n
Input resistance R _e	$410 \Omega \pm 6 \Omega$
Output resistance R _a	350 Ω ± 7 Ω
Insulation resistance R _{is}	≥ 5000 MΩ
Rated temperature range B _{tn}	-10 to +40 °C
Operating temperature range B _{tu}	-40 to +80 °C
Storage temperature range B _{ts}	-40 to +90 °C
Sensor material (DIN)	Edelstahl 1.4542
Degree of protection to DIN EN 60529,	IP 66/68
IEC 60529	
Max. tightening torque of the fixing screws	6 Nm
Current calibration ²	Standard
EEx (i) certification 3)	EEx ib II C T6

See the data sheet for technical data of unlisted load cells.

¹⁾ For rated temperature –10 to +40 °C
²⁾ Current calibration: nominal characteristic value and output resistance are adjusted so that the output current is calibrated within 0.05 % of a reference value. This makes it easier to connect several load cells in parallel.

³⁾ Optional

5.2 Unit Version

SIWAREX R load cells are made of high-grade steel as a standard. They are hermetically sealed which allows them to be used in a rugged or aggressive environment. Their compact structure makes them mostly easy to install. SIWAREX R load cells are licensed for use in scales with mandatory calibration of class III DIN EN 45501 and comply with OIML R60 3000d. SIWAREX R load cells are available alternatively with EEx (i) approval for

applications in hazardous areas.

The connecting cables are generally 4-wire cables.

The above specifications do not apply for the K series and load cells outside the standard scope of delivery.

The housing of the SIWAREX R high-load cells of the K series are made of varnished steel.

Descriptions of load cell models not belonging to the standard delivery program can be found in the respective data sheet.

5.3 Explosion Protection

Only load cells and components with the appropriate Ex approval may be used in hazardous areas. SIWAREX R load cells are approved according to

II 2 G EEx ib II C T6 or T4

II 3 G EEx nA II T6 or T4

II 3 G EEx nL IIC T6 or T4

II1D T70°C

II2D T70°C

II3D T70°C

. The K series and load cell types outside the standard scope of delivery are exceptions.

The circuits of the load cells of series CC must be considered grounded. They are equipped with an integrated overload protection as standard. For this reason, they cannot be tested for dielectric breakdown with 500 VAC.

To connect the load cells in the hazardous area, the EC type examination certificates KEMA 00ATEX1133X and KEMA 00ATEX1134X, and their supplements, must be observed.

NOTE

If an Ex-approved load cell i used in a non-hazardous area, the license is annulled. The Ex label must be endorsed. The load cell may no longer be used in a hazardous area.



WARNING

To be observed when using in hazardous areas:


- The decree governing electrical systems in hazardous rooms (according to the valid national standard, in Germany ElexV §§ 9,15).
- The conditions for installing electrical systems in hazardous areas DIN EN 60079-14 (VDE0165) or DIN EN1127-1.
- The specifications of the EC certificate of conformity.
- All work on electrical circuits for systems where there is a risk of explosion must be performed by qualified personnel.

5.4 Electromagnetic Compatibility

To maintain EMC, e.g.


- an EMC-compatible laying of cables (also inside cabinets) must be observed.
- the signal cable must be laid separately from cables with voltages > 60 V or high currents.
- the vicinity of large electrical installations must be avoided.
- shielded cables must be used.
- proper grounding must be observed.

5.5 Dimensions




Nennlast	ØA	ØB	ØС	D
10 – 200 kg	8,2	8,2 ^{+0,1}	23,0	20,0
350 kg	10,3	10,3 ^{+0,1}	24,0	19,0

Figure 5-1 BB series




Rated load	Α	В	С	D	Е	ØF	G	Н	J	ØK	ØL	М
0,5 – 2 t	203,2	36,5	98,4	63,5	19,1	30,2+0,2	36,5	11,9	47,6	17,5 ^{H11}	14	101,6
5 t	235,0	47,5	123,8	66,7	20,6	41,3 ^{+0,2}	47,6	15,8	69,9	25,5 ^{H11}	22	111,2

Figure 5-2 SB series




Rated load	ØA	В	ØС	ØD	E	ØF	G	Max. tightening torque [Nm]	K	ØL
60, 130, 280 kg	63	22	15,1	3,2	15	55,5	M5	8	34	6,5
0,5, 1 t	80	25	19	M10	-	70	M6	13	17,5	6,2
2, 3,5, 5 t	80	30	19	15 ^{H7}	-	70	M6	13	17,5	6,2
10 t	95	35	29,1	24,9	-	-	-	-	17,5	6,2
13 t	95	35	29,1	24,9	20	-	-	-	40	6,5

Figure 5-3 RN series 60 kg to 13 t




Rated load	ØA	В	ØС	Е
28 t	120	46	35,9	25
60 t	140	62	47,9	34

Figure 5-4 RN series 28 und 60 t



Rated load	ØA	В	С	ØD	E	F	G	ØН	J	SRK
10 t; 25 t	73,0	82,5	12,0	58,0	6,5	1,8	64,0	31,8	M12x1,75	152
									11 deep	
40 t; 60 t	105,0	127,0	34,0	82,5	8,0	11,0	87,0	58,7	M20x2,5	152
									20 deep	
100 t	152,4	184,2	72,3	123,8	23,6	21,8	108,2	79,2	M20x2,5	432
									20 deep	

Figure 5-5 CC series



Rated load	Ød	ØD	Н	K	L	SRA
2,8t	16,7	45	40	54	56	50
6 t	16,7	45	40	54	56	50
13 t	24,5	55	44	59	68	66
28 t	36	64	46	63,5	74	72
60 t	52,7	90	50	76,5	90	100
130 t	77,5	121	64	92	116	125
280 t	114	165	80	114	170	183

Figure 5-6 K series




Figure 5-7 SP series

See data sheet for dimensions of unlisted load cells.

Ordering Data 6

BB series

Verification capability to OIML R60 up to 3000 d, Connecting cable3 m4) (4-wire)

Order No.:	7MH4 103 -	•	•	С	•	1
Nominal load:	10 kg	2	Å			
	20 kg	2	D			
	50 kg	2	K			
	100 kg	3	Α			
	200 kg	3	D			
	350 kg ¹⁾	3	G			
Explosion protection						
 Without 					Ò	
With degree of protection EEx ib II C T6 for					1	

connection to intrinsically-safe circuits

CC series

Verification capability to OIML R60 up to 3000 d, Connecting cable (4-wire)

Order No.:	7M	H4 106 -	•		•	•	1
	connecti	ng cable					
Nominal load:	10 t Lengtl	า ⁴⁾ ์: 10 m	5	Α	С		
	25 t		5		С		
	40 t	20 m	5	Н	С		
	60 t	20 m	5	L	С		
	100 t ²⁾	20 m	6	Α	Α		
Explosion protection							
 Without 						0	
With degree of protection EEx ib II C T6 for connection to intrinsically-safe circuits						1	



SB series

Verification capability to OIML R60 up to 3000 d, Connecting cable5 m4) (4-wire)

Order No.:	7MH4 105 -	•	•	С	•	1
Nominal load:	500 kg	3	K			
	1 t	4	Α			
	2 t	4	D			
	5 t	4	K			
Explosion protection						
 Without 					0	
With degree of protection EEx ib II C T6 for connection to intrinsically-safe circuits						



K series


Accuracy class 0.2, Without explosion protection, connecting cable 3) (4-wire)

Order No.:		7MH3 105 -	*	•	C0
	CC	onnecting cable			
Nominal load:	2,8 t	Length ⁴⁾ : 5 m	Ż	À	
	6 t	5 m	3	Α	
	13 t	10 m	1	В	
	28 t	10 m	2	В	
	60 t	10 m	3	В	
	130 t	10 m	1	С	
	280 t	10 m	2	С	
	280 t	10 m	2	С	




RN series

Verification capability to OIML R60 up to 3000 d, Connecting cable (4-wire)





SP series
Verification capability to
OIML R60 up to 3000 d,
Connecting cable (6-wire)



- 1) Mounting accessories on request.
 2) Verification capability to OIML R60 up to 1000 d.
- 3) Cables heat-resistant: -60 °C to +180 °C.
 4) Length tolerance: +/- 100 mm; cable length 20 m or more: +/- 300 mm.

Furhter models of load cells on inquiry.